

TECHSPEC® 100mm Length, T-Mount Extension Tube



Stock **#65-969** **3 In Stock**

⊖ 1 ⊕ £77⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£77.20 each
Qty 5-9	£68.56 each
Qty 10-25	£63.52 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Extension Tube **Type:**

Extension Tube (Fixed) **Function:**

Note:
Inner threads are female T-Mount (M42 x 0.75), allowing optical components to be mounted with [#58-741](#)

Physical & Mechanical Properties

100.0 **Extension Length (mm):**

103.45 **Total Length (mm):**

37.0 **Clear Aperture CA (mm):**

48.0 **Outer Diameter (mm):**

Threading & Mounting

T-Mount **Thread Type:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

;