

1.00" x 11.9", 0.75" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock #46-110 **20+ In Stock**

⊖ 1 ⊕ £50⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£50.40 each
Qty 11-49	£45.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fresnel Lens **Type:**

Physical & Mechanical Properties

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

1.0 x 11.9 **Dimensions (inches):**

25.4 x 302.26 **Dimensions (mm):**

0.75 x 11.9 **Effective Size (inches):**

±0.020 **Thickness Tolerance (inches):**

Optical Properties

19.05 **Effective Focal Length EFL (mm):**

Acrylic **Substrate:**

Uncoated **Coating:**

400 - 1100 **Wavelength Range (nm):**

0.75 **Effective Focal Length EFL (inches):**

200.00 **Groove Density (grooves/inch):**

1.49 **Index of Refraction (n_d):**

85 (Typical) **Transmission (%):**

Environmental & Durability Factors

80 (Maximum) **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 242:**

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

