

1064nm Flat Top Beam Shaper | π Shaper 12_12_1064_HP

See More by [AdlOptica](#)



Stock **#15-495** [CONTACT US](#)

-

1

+

£7,148.50

ADD TO CART

Qty 1-4

£7,148.50

Qty 5+

£6,435.35

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):

1064

Diameter (mm):

42.00

Entrance Beam Diameter, 1/e² (mm):

12.0 - 12.1

Model Number: πShaper 12_12_1064_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 1020 - 1100
Style: Flat Top
Damage Threshold, By Design: ☐ 3 J/cm² @ 5ns (typical)
Output Diameter, FWHM (mm): 12.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant