

# 10mm Aperture, 38mm FL UV/VIS Fiber Refocusing Assembly



Fiber Refocusing Assembly



Stock **#88-187** [CONTACT US](#)

- 1 +

**£263.50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| £263.50                       |
| Qty 11+                       |
| £232.47                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
15.88

Substrate: ☐  
[Fused Silica](#) (Corning 7980)

|                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Type:</b><br>Refocusing Assembly                                                                                                                       |
| <b>Wavelength Range (nm):</b><br>190 - 1250                                                                                                               |
| <b>Aperture Size:</b><br>10.0                                                                                                                             |
| <b>Focal Length FL (mm):</b><br>38.00                                                                                                                     |
| <b>Housing Material:</b><br>Anodized Aluminum                                                                                                             |
| <b>Length (mm):</b><br>16.38                                                                                                                              |
| <b>Note:</b><br>Compatible with <a href="#">#88-180</a> , <a href="#">#88-181</a> , <a href="#">#88-190</a> , & <a href="#">#88-191</a> Fiber Collimators |
| <b>Operating Temperature (°C):</b><br>-40 to 100                                                                                                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

