

10mm Aperture UV/VIS Fiber Optic Collimator, SMA



Fiber Optic Collimator, SMA (SMA adapter inserted)



Stock **#88-181** [CONTACT US](#)

-

1

+

£314.50

ADD TO CART

Qty 1-10

£314.50

Qty 11+

£277.95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

15.88

Substrate:

[Fused Silica](#) (Corning 7980)

Type: Fiber Collimator
Wavelength Range (nm): 190 - 1250
Aperture Size: 10.0
Compatible Fiber NA: 0.22
Connector: SMA
Fiber Diameter (µm): compatible 400 to 800
Focal Length FL (mm): 18.00
Housing Material: Anodized Aluminum
Length (mm): 34.29
Note: Compatible with #88-182 , #88-183 , #88-184 , #88-185 , #88-186 , & #88-187 Refocusing Assemblies
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View