

10mm Aperture VIS/NIR Fiber Optic Collimator, FC



Fiber Optic Collimator, FC (FC adapter inserted)



Stock **#88-190** 3-4 DAYS

⊖ 1 ⊕

£187.00

ADD TO CART

Qty 1-10

£187.00

Qty 11+

£164.90

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
15.88

Substrate: ☐
[N-BK7](#)

Type: Fiber Collimator
Wavelength Range (nm): 350 - 2200
Aperture Size: 10.0
Compatible Fiber NA: 0.22
Connector: FC
Fiber Diameter (µm): compatible 400 to 800
Focal Length FL (mm): 18.00
Housing Material: Anodized Aluminum
Length (mm): 34.29
Note: Compatible with #88-182 , #88-183 , #88-184 , #88-185 , #88-186 , & #88-187 Refocusing Assemblies
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View