

TECHSPEC[®] 10mm Uncoated, Rhomboid Prism



Stock **#47-213** ☐ In Stock

-

1

+

£142.38

ADD TO CART

Qty 1-5

£142.38

Qty 6+

£113.90

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Length (mm):
10.00

Coating:
Uncoated

Angle Tolerance (arcsec):
±5

Beam Deviation (arcsec): ±30
Dimensional Tolerance (mm): ±0.1
Image Orientation: Beam Deviation
Ray Deviation (°): 0.00
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Rhomboid Prism
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View