

10X Objective, Nikon CFI Plan Fluor

See More by [Nikon](#)



10X Objective, Nikon CFI Plan Fluor, #88-379

Stock **#88-379** **4 In Stock**

-

1

+

£812^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£812.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Model Number:	MRH00105
Compatible Tube Lens Focal Length (mm):	Focal Length: 200mm
Type:	Microscope Objective
Style:	Infinity Corrected


Manufacturer:		Nikon
Physical & Mechanical Properties		
Field of View (mm):		2.5
Length excluding Threads (mm):		42.40
Maximum Diameter (mm):		30
Weight (g):		150.00
Optical Properties		
Compatible Cover Glass Thickness (mm):		0.17
Horizontal Field of View, 1/2" Sensor:		0.64mm
Horizontal Field of View, 2/3" Sensor:		0.88mm
Magnification:		10X
Numerical Aperture NA:		0.30
Working Distance (mm):		16.0
Field Number (mm):		25
Parfocal Length (mm):		58.4
Immersion Liquid:		N/A
Sensor		
Maximum Sensor Format:		2/3"
Threading & Mounting		
Mounting Threads:		M25 x0.75
Regulatory Compliance		
RoHS 2015:		Exempt
Reach 224:		Contains SVHC(s)
Certificate of Conformance:		View

Product Details

- Provide High Contrast Fluorescence Observation
- Ideal for Multiple Microscopy Techniques
- High Transmission from UV to the IR

Nikon CFI Plan Fluor Objectives feature high transmission from the ultraviolet to the infrared, along with exceptional flatness across the entire field of view. These objectives are ideal multipurpose objectives for a variety of microscopy techniques, including brightfield, fluorescence, polarizing, or DIC microscopy. These microscope objectives are suitable for high contrast fluorescence observation or for applications including photomicrography. Nikon CFI Plan Fluor Objectives have M25 x0.75 mounting threads. The objectives are available in magnifications from 4X up to 60X.

Technical Information



Dimensions (mm)								
Stock No.	Nikon Model Number	Immersion Liquid	Magnification	Parafocal Length	A	B	C	D
#88-378	MRH00041	N/A	4X	60.06	30.0	42.7	16.5	M25 x 0.75
#88-379	MRH00101	N/A	10X	60.06	30.0	42.4	18.0	M25 x 0.75
#38-004	MRP07220	Water	16X	75.0	35.0	72.0	6.0	M32 x 0.75
#88-380	MRH00201	N/A	20X	60.06	28.0	57.8	8.5	M25 x 0.75
#88-381	MRH00405	N/A	40X	60.06	30.0	59.2	10.0	M25 x 0.75
#88-382	MRH00602	N/A	60X	60.06	31.5	59.2	5.0	M25 x 0.75

;