

TECHSPEC® 1:1.43 with 14mm and 20mm EFL Achromats, 15mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#43-993** 3-4 DAYS



1



£155.13

ADD TO CART

Qty 1-5

£155.13

Qty 6+

£124.10

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
9.5

Center Air Spacing (mm):
1.33

Substrate: ☐
[N-BAF10](#) / [N-SF5](#) / [S-BAH11](#) / [N-SF10](#)

Surface Quality: 40-20
Working f#: f/1.98
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Effective Focal Length EFL A (mm): 14.00
Effective Focal Length EFL B (mm): 20.00
Housing Diameter (mm): 15 +0.0/-0.10
Housing Length (mm): 21 ±0.2
Lens Edge Spacing at Mount (mm): 4
Magnification: 1:1.43
Object Distance (mm): 7.11
Image Distance (mm): 26.7
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View