

[See all 23 Products in Family](#)

# 12", Green 530nm, UltraSeal Washdown Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Bar Lights

Stock **#18-632** CLEARANCE **2 In Stock**

⊖ 1 ⊕ £1,104<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | £1,104.00 each                |
| Need More? | <a href="#">Request Quote</a> |

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

AL247M12-530IC **Model Number:**

50000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

**Note:**  
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

|                       |                           |
|-----------------------|---------------------------|
| Advanced Illumination | <b>Manufacturer:</b>      |
| Bar Light             | <b>Geometry:</b>          |
| Constant              | <b>Illumination Mode:</b> |

## Physical & Mechanical Properties

|                   |                         |
|-------------------|-------------------------|
| 323.8 x 42.9 x 24 | <b>Dimensions (mm):</b> |
| 657               | <b>Weight (g):</b>      |

## Optical Properties

|       |                         |
|-------|-------------------------|
| Green | <b>Color:</b>           |
| 530   | <b>Wavelength (nm):</b> |

## Electrical

|       |                               |
|-------|-------------------------------|
| 0.70A | <b>Minimum Input Current:</b> |
|-------|-------------------------------|

## Hardware & Interface Connectivity

|              |                           |
|--------------|---------------------------|
| Flying Leads | <b>Connector:</b>         |
| 24V          | <b>Input Voltage (V):</b> |

|   |
|---|
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#89-513</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
|---|

## Environmental & Durability Factors

|        |                                    |
|--------|------------------------------------|
| 0 - 60 | <b>Operating Temperature (°C):</b> |
| IP69K  | <b>Environmental Rating:</b>       |

## Regulatory Compliance

|                                  |                                    |
|----------------------------------|------------------------------------|
| <a href="#">Exempt</a>           | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>             | <b>Certificate of Conformance:</b> |
| <a href="#">Contains SVHC(s)</a> | <b>Reach 233:</b>                  |

## Product Details

- IP69K Certified for Extreme Washdown Environments
- Stainless Steel Housing
- High Intensity Output up to 70,200 Lux
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Advanced Illumination UltraSeal Washdown Bar Lights offer intense, direct illumination up to 70,200 Lux while providing maximum protection in extreme environmental conditions. These IP69K certified Bar Lights were designed with a crevice-free design to withstand high temperature wash-down procedures and material buildup. The 316 stainless steel is FDA compliant, making them a suitable option for food or pharmaceutical inspection environments. Advanced Illumination UltraSeal Washdown Bar Lights are ideal for hygienic and aseptic manufacturing applications, such as prolonged liquid immersion and high-pressure steam cleaning common in food and beverage inspection and processing.

**Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.