

TECHSPEC[®] 12.0mm Dia. x 84.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock **#47-340-INK** 3-4 DAYS
[Other Coating Options](#)

-

1

+

£43.77

ADD TO CART

Qty 1-9
£43.77
Qty 10+
£39.31
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 ±0.025

Effective Focal Length EFL (mm):

84.00 @ 587.6nm
Back Focal Length BFL (mm): 82.39
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.05
Edge Thickness ET (mm): 2.08
Radius R₁ (mm): 43.43
Clear Aperture CA (mm): 11
f/#: 7
Numerical Aperture NA: 0.07
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View