

(12.5-75mm FL), 6X Manual Zoom Video Lens



#53-153

Stock #53-153 3-4 DAYS



1



£497.25

ADD TO CART

Qty 1+

£497.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
495 - 86

Length (mm):
114.50

Horizontal Field of View, 1/2" Sensor:
27.8° - 4.9°

Filter Thread:
M55.0 x0.75

Maximum Diameter (mm):

57.00
Weight (g): 475.00
Zoom Ratio: 6:1
Type: Zoom Lens, Macro
Focal Length FL (mm): 12.50 - 75
Maximum Sensor Format: 2/3"
Working Distance (mm): 1,000 - ∞
Mount: C-Mount
Aperture (f/#): f/1.2 - f/16
Lens Wavelength Range: VS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View