

TECHSPEC® 12.5" Diameter x 125" FL Uncoated, Parabolic Mirror



Stock **#35-730-000** 3-4 DAYS

- 1 + **£2,435.25**

ADD TO CART

Qty 1-2
£2,435.25
Qty 3+
£2,069.75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 125.0
Effective Focal Length EFL (mm): 3,175.00
Radius of Curvature (mm): 6,350.00
Aperture (f/#): f/10
Coating: Uncoated
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View