

TECHSPEC® 12.5mm Diameter x 75mm FL Uncoated, UV PCX Cylinder Lens



Stock **#68-170** CLEARANCE 3-4 DAYS

- 1 + **£84.96**

ADD TO CART

Qty 1+

£84.96

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f/#:
6.00

Numerical Aperture NA: 0.08
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 200 - 2200
Back Focal Length BFL (mm): 73.63
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 1.43
Focal Length Tolerance (%): ±3
Radius R (mm): 34.39
Surface Quality: 40-20
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View