

TECHSPEC® 125mm, English Z-Stage



TECHSPEC® Vertical Translation Stages



Stock **#66-506** [CONTACT US](#)

-

1

+

£872^{.00}

ADD TO CART

Volume Pricing	
Qty 1-2	£872.00 each
Qty 3+	£760.64 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

English

Physical & Mechanical Properties

Linear (Z)	Type of Movement:
Crossed Roller Bearing	Guide System:
125 x 125	Stage Size (mm):
20	Travel (mm):
1/4-20	Center Hole:
Aluminium Stage	Construction:
0.5	Leadscrew Pitch (mm):
5	Load Capacity (kg):
4.92 x 4.92	Stage Size (inches):
3	Straight Line Accuracy (µm):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting

Mounting Threads:
(21) 1/4-20, (4) 6-32, (8) 2-56

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

70mm and 125mm stages mount directly and do not require bottom adapter plates.

- Mechanically Compatible with our **TECHSPEC® Stages**
- Fine Micrometer Movement
- Locking Screw on Stages

Our newly developed precision TECHSPEC® Vertical Translations Stages (Z-axis stages) feature a unique and advanced crossed roller bearing guide system that provides high accuracy, rigidity and load capacity. Each stage is designed to integrate with our line of [TECHSPEC® stages](#) in order to provide flexibility in allowing the user to create a number of multi-axis configurations. These stages have a locking screw and fine micrometer movement. TECHSPEC® Vertical Translations Stages are constructed of aluminum and have a linear (Z) movement. The stages are available in both English and Metric versions and are offered in four sizes.

TECHNICAL INFORMATION

