

TECHSPEC[®]

12.5mm H x 25mm L x -150mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC[®] Illumination Grade PCV Cylinder Lenses

Stock #68-060 3-4 DAYS

-

1

+

£52.70

ADD TO CART

Qty 1-5

£52.70

Qty 6+

£42.07

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-150.00

Substrate: 
[N-BK7](#)

Coating:

Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -151.65
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 2.73
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -77.52
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View