See all 6 Products in Family

125mm Sq. English Kinematic Magnetic Base

Stock **#22-403** CONTACT US

- 1 + **£298.40**

ADD TO CART

Volume Pricing	
Qty 1-9	**£298.40** each
Qty 10+	**£269.20** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
English

Note:
The permanent magnet is turned on and off by integrated screw (5mm Hex)

Switchable:
Yes

Physical & Mechanical Properties

Length (mm):
125.00

Width (mm):
125.00

Thickness (mm):
25.40

Construction:
Anodized Aluminum

Weight (kg):
0.97

Repeatability (µrad):
<70.0

Threading & Mounting

Mounting Threads:
(71) 1/4-20

Material Properties

Magnetic Force (N):
40

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with **TECHSPEC Stages**

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our **TECHSPEC stages**, making them an ideal lab bench component for system building.

;