

12.7mm Dia. UHR Broadband Dielectric Mirror, 750-1100nm



Stock **#17-497** CLEARANCE 3-4 DAYS

- 1 + **£199.71**

ADD TO CART

Qty 1+
£199.71

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.70 +0.00/-0.10

Surface Flatness (P-V):
λ/10

Substrate:
[Fused Silica](#) (Corning 7980)

Surface Quality:
10-5

Coating Specification:
R_{abs} >99.9% @ 750 - 1100nm (45°, s-pol)

R _{abs} >99.9% @ 750 - 1100nm (45°, p-pol)	
Coating:	UHR Dielectric Mirror (750-1000nm)
Coating Type:	Dielectric
Angle of Incidence (°):	45
Clear Aperture CA (mm):	9.20
Edges:	Ground
Parallelism (arcmin):	<3
Thickness (mm):	6.35 ±0.20
Type:	Flat Mirror
Wavelength Range (nm):	750 - 1100

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View