

TECHSPEC® 12.7mm Dia. x 25.4mm FL, Uncoated, Plano-Convex Lens



Stock **#49-842** ☐ In Stock
[Other Coating Options](#)

1 **£23.80**

ADD TO CART

Qty 1-9
£23.80
Qty 10+
£21.46
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):

25.40 @ 587.6nm
Back Focal Length BFL (mm): 23.43
Coating: Uncoated
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.36
Radius R₁ (mm): 13.13
Clear Aperture CA (mm): 11.7
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View