

12.5/12.7mm Optic Dia., X-Y Translating Optic Mount



5 Axes Optical Mount



Stock #62-955 10 In Stock

-

1

+

£208^{.80}

ADD TO CART

Volume Pricing	
Qty 1-4	£208.80 each
Qty 5-9	£198.48 each
Qty 10+	£177.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Adjustable - Linear (XY)	Type:
Circular	Type of Optics:
Physical & Mechanical Properties	
10.0	Clear Aperture CA (mm):
64.0	Outer Diameter (mm):
20.00	Thickness (mm):
±1.5 in X and Y	Travel (mm):
180	Weight (g):
Black Anodized Aluminum	Construction:
Threading & Mounting	
12.5 - 12.7	Size of Compatible Optics (mm):
15.0 (Max)	Thickness of Compatible Optics (mm):
M6 x 1.0	Compatible Post:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

PRODUCT DETAILS

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
 - Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
 - M6 Mounting Threads
- Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

TECHNICAL INFORMATION

