

12.9mm Dia. x 14mm FL, Aspheric Condenser Lens



Stock **#19-513** 3-4 DAYS

[Other Coating Options](#)

- 1 + **£28.90**

ADD TO CART

Qty 1-10
£28.90

Qty 11+
£26.35

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.90 +0.0/-0.2

Effective Focal Length EFL (mm):
14.00

Numerical Aperture NA:
0.46

Back Focal Length BFL (mm): 10.2
Substrate:  H-K9L
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 11.61
Edge Thickness ET (mm): 2.52
Center Thickness CT (mm): 5.70 ±0.30
f/#: 1.09
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 12.9
Radius R ₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 330 - 2000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View