

12mm Dia x -6.1mm FL Enhanced Aluminum Coated, Convex Mirror



Stock **#64-055** 3-4 DAYS

- 1 + **£34.00**

ADD TO CART

Qty 1-5
£34.00
Qty 6+
£30.60
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.00 +0.00/-0.10

Focal Length FL (mm):
-6.10

Center Thickness CT (mm):
3.00

Clear Aperture (%):

Coating:
Enhanced Aluminum (450-650nm)

Coating Specification:
R_{avg} >95% @ 450 - 650nm

Coating Type:
Metal

Edge Thickness ET (mm):
1.41

Focal Length Tolerance (%):
±2

Radius R (mm):
12.11

Substrate: 
[N-SF5](#)

Surface Quality:
60-40

Type:
Spherical Mirror

Wavelength Range (nm):
450 - 650

Damage Threshold, Reference: 
0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
