

12mm Fixed Focal Length Lens



#86-206

Stock **#86-206** [CONTACT US](#)



1



£1,687.25

ADD TO CART

Qty 1+

£1,687.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
182.00

Iris Option:
Variable

Length (mm):
85.00

Filter Thread:
M55.0 x0.75

Maximum Diameter (mm):

57.0
Weight (g): 270.00
Maximum Image Circle (mm): 21.60
Horizontal Field of View @ Max Sensor Format: 74.9
Type: Fixed Focal Length Lens
Focal Length FL (mm): 12.00
Maximum Sensor Format: 4/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/2 - f/22
Distortion (%): <0.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)