

12" x 11.5" 0°, Glossy, 3M Light Control Film



Stock #52-385 3-4 DAYS

- 1 + **£134.30**

ADD TO CART

Qty 1+

£134.30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ Polycarbonate

Length (mm):
304.80

Operating Temperature (°C):
-40 to +120

Dimensions (inches):
12 x 11.5

Dimensions (mm): 304.8 x 292.1
Thickness (inches): 0.021
Thickness (mm): 0.50
Type: Specialty Window
Width (mm): 292.10

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View