

13mm Travel, Metric Micrometer, Solid Top Ball Bearing Stage



45mm/1.75" Center drive stages and optional brackets

Stock **#55-281** 3-4 DAYS

-

1

+

£495.55

ADD TO CART

Qty 1+

£495.55

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Metric Micrometer

Drive Orientation:
Center Drive

Type:

Metric
Stage Size (mm): 44.4 x 44.4
Travel (mm): 13
Construction: Aluminium Stage
Graduation (mm): 0.01
Height (mm): 19.1
Load Capacity, Normal (kg): 11
Load Capacity, T_a (kg): 4.5
Note: Solid Top
Straight Line Accuracy (µm): 2 per 25mm of travel
Weight (kg): 0.23
Thrust Capacity, T_a (kg): 4.5
Thrust Capacity, T_b (kg): 2.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View