

14 Gauge (50 Count), UV Blocking Tapered Tips



14 Gauge (50 Count), UV Blocking Tapered Tips, #55-060

Stock **#55-060** 5 In Stock

-

1

+

£52⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£52.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

14 Gauge, Olive Color

Type:

Physical & Mechanical Properties

1.55

Inner Diameter (mm):

1.83

Outer Diameter (mm):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Empty Barrels are Available in Clear, Amber, and Opaque Versions
 - Tips are Available in Plastic and Steel
 - [Dispensing Guns](#) and [Pre-Loaded Norland Adhesive Barrels](#) are Also Available
- Dispenser barrels, tips, and other accessories are available for use with dispensing guns and hand plungers. Dispenser Barrels are available in a clear version for normal fluids, an amber version for UV-curing fluids, and an opaque version for light sensitive fluids. Dispenser tips are available in plastic and steel to ensure varying levels of controllable deposits without leakage.
- Note:** Barrels, tips, and adhesive are sold separately from [dispensers](#). [Pre-loaded Norland adhesive barrels](#) are also available.