

14mm Dia. x -21mm FL, Negative Meniscus Lens, Grade 2



Stock **#96-202** CLEARANCE **20+ In Stock**

-

1

+

£4^{.20}

ADD TO CART

Volume Pricing	
Qty 1+	£4.20 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

Diameter (mm):

14.00

Optical Properties

Effective Focal Length EFL (mm):

-21.00

f/#:

1.5

Numerical Aperture NA:

0.33

Material Properties	
Grade 2	Grade:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Experimental Quality Negative Meniscus Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

