

152mm Dia x 17mm FL Alum. Coated, Parabolic Reflector



Stock **#68-792** [CONTACT US](#)

- 1 + **£644.30**

ADD TO CART

Qty 1-10
£644.30

Qty 11+
£569.92

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: [BOROFLOAT®](#)

Diameter (mm):
152.00 +0.0/-0.5

Focal Length FL (mm):
17.00

Aperture (f/#):

0.112
Coating: Protected Aluminum (400-700nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating Type: Metal
Center Hole Diameter (mm): 30.0
Height (mm): 79.0
Type: Parabolic Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View