

8.5mm Max. Aperture, Iris Diaphragm



Stock #42-124 3-4 DAYS

-

1

+

£56.10

ADD TO CART

Qty 1-4
£56.10
Qty 5+
£49.73
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.0

Maximum Aperture (mm):
8.5

Outer Diameter (mm):

15.5
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 8.00
Number of Leaves: 9.00
Thickness (mm): 5.30

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant