

15° Diffusing Angle 12.5mm Unmounted



Stock #35-864 CLEARANCE 3-4 DAYS

-

1

+

£76.50

ADD TO CART

Qty 1-5
£76.50
Qty 6+
£57.38
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):
±1.5

Diffusing Angle (°):
15 (FWHM)

Diameter (mm):
12.50

Dimensional Tolerance (mm):

±0.5
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant