

TECHSPEC[®] 15mm 50R/50T NIR Cube Beamsplitter



Stock #14-641 3-4 DAYS

-

1

+

£175.95

ADD TO CART

Qty 1-5

£175.95

Qty 6+

£140.67

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Coating:
λ/4 MgF₂ @ 900nm on Faces
Multilayer Dielectric on Hypotenuse

Construction: Cube
Dimensions (mm): 15.0 x 15.0 x 15.0 ±0.10
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Standard Beamsplitter
Wavelength Range (nm): 700 - 1100

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View