

TECHSPEC®

15mm Dia. x 22.5mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock **#45-880-INK** [CONTACT US](#)

-

1

+

£46.75

ADD TO CART

Qty 1-9
£46.75
Qty 10+
£42.07
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.00

Back Focal Length BFL (mm):
21.29

Effective Focal Length EFL (mm): 22.50
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.20
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.54
Radius R₁=R₂ (mm): 34.36
Clear Aperture CA (mm): 14.00
f/#: 1.5
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View