

15mm Diameter 220 Grit Ground Glass Diffuser



Stock #45-652 **20+ In Stock**

⊖ 1 ⊕ £19⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£19.20 each
Qty 11+	£17.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Ground Glass Diffuser **Type:**
Sandblasted on first surface **Note:**

Physical & Mechanical Properties

15.00 ±0.25 **Diameter (mm):**

Ground	Edges:
220	Grit: <input type="checkbox"/>
1.60	Thickness (mm):

Optical Properties

Uncoated	Coating:
Float Glass	Substrate: <input type="checkbox"/>
350 - 2000	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



[Quote Your Size](#)

[Compatible Mounts](#)