

TECHSPEC[®] 15mm, Uncoated, Fused Silica, Right Angle Prism



TECHSPEC UV Fused Silica Right Angle Prisms

Stock #45-184 3-4 DAYS

-

1

+

£76.50

ADD TO CART

Qty 1-5

£76.50

Qty 6+

£61.20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[Fused Silica](#) (Corning 7980)

Surface Quality:

60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.10 Legs
Angle Tolerance (arcmin): ±5
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 21.20
Length of Legs (mm): 15.00
Pyramid Tolerance (arcmin): ±5
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): $\lambda/2$

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View