

TECHSPEC® 15mm, VIS 0° Coated, Rhomboid Prism



Stock **#49-422** ☐ In Stock

- 1 + **£157.25**

ADD TO CART

Qty 1-5
£157.25

Qty 6+
£125.80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Length (mm):
15.00

Coating:
VIS 0° (425-675nm)

Angle Tolerance (arcsec):
±5

Beam Deviation (arcsec): ±30
Coating Specification: R_{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): ±0.1
Image Orientation: Beam Deviation
Ray Deviation (°): 0.00
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Rhomboid Prism
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: Entrance/Exit Surfaces: 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View