

15mW Random Polarization, Lasos HeNe Laser



Stock #35-213 3-4 DAYS

-

1

+

£1,206.15

ADD TO CART

Qty 1+
£1,206.15

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Output Power (mW): 15
Polarization: Random
Wavelength (nm): 632.80
Weight (g): 930.00
Laser Class - IEC: 3B

Power Supply: Power Supply Required and Sold Separately. USA: #35-223 Europe: #35-223 Japan: Not Available Korea: Not Available China: Not Available
Static Alignment: Centered to Outer Cylinder: ≤0.5mm Parallel to Outer Cylinder: ≤1
Pointing Stability (mrad/°C): ≤0.05
RMS Noise: 30Hz—10MHz ≤1%
Beam Diameter (mm): 1.00
Type of Laser: HeNe
Beam Divergence (mrad): ≤1.0
Laser Class - CDRH: IIIb
Length (mm): 637.00
Longitudinal Mode Spacing, Nominal (MHz): 257.00
Diameter of Laser Head (mm): 45
Length of Laser Head (mm): 637

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View