

[See all 7 Products in Family](#)

TECHSPEC® 15X, 0.19 NA, UCf Objective



Stock #26-689 [CONTACT US](#)

- 1 + £292⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	£292.80 each
Qty 3-4	£272.80 each
Qty 5-9	£263.20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fluorite **Type:**

Finite Conjugate **Style:**

Manufacturer:

Physical & Mechanical Properties

Length (mm):

118.63

Maximum Diameter (mm):

29

Weight (g):

105

Optical Properties

Horizontal Field of View, 2/3" Sensor:

0.58

Horizontal Field of View, 1.1" Sensor:

0.938

Focal Length FL (mm):

8.00

Magnification:

15X

Numerical Aperture NA:

0.19

Resolving Power (μm):

3.51

Depth of Field (μm):

7.42

Working Distance (mm):

7.8

Wavelength Range (nm):

400 - 700

Field Number (mm):

17.6

Sensor

Maximum Sensor Format:

1.1"

Threading & Mounting

Mounting Threads:

C-Mount

Environmental & Durability FactorsOperating Temperature ($^{\circ}\text{C}$):

+10 to +40

Regulatory Compliance

Certificate of Conformance:

[View](#)**Product Details**

- Compact Finite Conjugate Objectives
- Mount Directly to a C-Mount Camera
- Near Diffraction Limited performance

TECHSPEC® UCf Objective Series are compact objectives that are finite conjugate by design, but achieve similar imaging performance of infinity corrected objectives and do not require a secondary tube lens to generate an image on the sensor. Available at 2X, 4X, 5X, 10X, 15X, and 20X magnifications. These objectives mount directly to a C-mount camera without additional extension tubes.