

17 x 23mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #31-417 3-4 DAYS

-

1

+

£14.45

ADD TO CART

Qty 1-5

£14.45

Qty 6+

£11.90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm): 17.0 x 23.0 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 1.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 23.00
Width (mm): 17.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant