

1.74mm FL, IR-Cut Filter at 650nm, f/2.8, Micro Video Lens



Stock #66-881 CLEARANCE CONTACT US

-

1

+

£26.35

ADD TO CART

Qty 1+

£26.35

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
19.60

Maximum Diameter (mm):
21.0

Maximum Image Circle (mm):
4.50

Horizontal Field of View @ Max Sensor Format:
114.4

Resolution, On-Axis:
124 lp/mm @20% Contrast

Resolution, 0.7 Field: 87 lp/mm @ 20% Contrast
Resolution, Full Field: 30 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 1.74
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mount)
Aperture (f#): f/2.8
Distortion (%): -60 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

Reach 205: Compliant
Certificate of Conformance: View