

1800 Grooves/mm, 50mm Square, VIS Holographic Grating



Reflective Holographic Gratings

Stock **#43-223** 3-4 DAYS



1



£306.00

ADD TO CART

Qty 1+

£306.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1800

Wavelength Range (nm):
400 - 700

Dimensions (mm):
50.0 x 50.0 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 50.00
Substrate: ☐ Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: VIS
Width (mm): 50.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 81
Peak Efficiency Avg, Typical (%): >65

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View