


TECHSPEC® 18mm Dia x 27mm FL Uncoated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#36-686** 3-4 DAYS

[Other Coating Options](#)



1



£110.50

ADD TO CART

Qty 1-5

£110.50

Qty 6+

£88.40

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm): 27.00 @ 587.6nm
Back Focal Length BFL (mm): 23.23
Coating: Uncoated
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 5.50 ±0.10
Edge Thickness ET (mm): 1.62
Radius R₁ (mm): 12.38
Clear Aperture CA (mm): 17
f/#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View