

TECHSPEC[®] 18mm Dia. x 27mm FL VIS-EXT, Inked, Double-Convex Lens



Stock **#89-166-INK** [CONTACT US](#)
[Other Coating Options](#)

-

1

+

£48.45

ADD TO CART

Qty 1-9
£48.45
Qty 10+
£43.56
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
18.00 ±0.025

Back Focal Length BFL (mm):
25.25

Effective Focal Length EFL (mm): 27.00
Coating: VIS-EXT (350-700nm)
Coating Specification: Ravg <0.5% @ 350 - 700nm
Substrate: N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.42
Radius R₁=R₂ (mm): 27.08
Clear Aperture CA (mm): 17.00
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View