

[See all 5 Products in Family](#)

## 19mm Dia x 476mm FL, Grade 1, Plano-Convex Lens



Stock #76-173 CLEARANCE **16 In Stock**

⊖ 1 ⊕ £8.<sup>20</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£8.20 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Plano-Convex Lens **Type:**

### Physical & Mechanical Properties

19.00 **Diameter (mm):**

### Optical Properties

476.00 **Effective Focal Length EFL (mm):**

Anti-Reflection Coating      Coating:

25.05      f#:

0.02      Numerical Aperture NA:

## Regulatory Compliance

[View](#)      Certificate of Conformance:

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

