

1" Travel, Eng Micrometer, Solid-Top Ball Bearing Stage



32mm/1.25" Side drive stage and its X-Y-Z configuration

Stock **#37-955** [CONTACT US](#)



1



£442.85

ADD TO CART

Qty 1+

£442.85

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
English Micrometer

Drive Orientation:
Side Drive

Type:

English
Stage Size (mm): 44.4 x 44.4
Travel (inches): 1
Length (mm): 55.37
Construction: Aluminium Stage
Graduation (inches): 0.001
Height (inches): 0.75
Height (mm): 19.1
Load Capacity, Normal (lbs): 25
Note: Solid Top
Stage Size (inches): 1.75 x 1.75
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.5
Thrust Capacity, T_a (lbs): 10
Thrust Capacity, T_b (lbs): 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View