

[See all 12 Products in Family](#)

## (2-3" Range), 0.0001", Mechanical Outside Micrometer, Ratchet Stop, Standard

See More by [Mitutoyo](#)



Stock #78-301 **1 In Stock**

⊖ 1 ⊕ £163<sup>20</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£163.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

±0.001 Accuracy (inches):

### General

2 - 3 inches Range:

103-217 Model Number:

## Physical & Mechanical Properties

Graduation (inches):

0.0001

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.