

2.0 OD M40.5 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-669 3-4 DAYS

- 1 + **£101.15**

ADD TO CART

Qty 1-9
£101.15

Qty 10+
£96.39

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
2.0

Clear Aperture CA (mm):
35.50

Filter Thread:
M40.5 x0.50

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 1.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View