

## 20 x 27mm, 70R/30T, Plate Beamsplitter



Stock **#46-695** 3-4 DAYS

- 1 + **£41.65**

ADD TO CART

|         |
|---------|
| Qty 1-9 |
| £41.65  |

|         |
|---------|
| Qty 10+ |
| £29.75  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Coating Specification:**  
Surface 1: Dielectric, ±5% R/T @ 550nm  
Surface 2: Uncoated

**Construction:**  
Plate

**Dimensional Tolerance (mm):**  
±0.38

|                                                                |
|----------------------------------------------------------------|
| <div>Dimensions (mm):<br/>20.0 x 27.0</div>                    |
| <div>Edges:<br/>Cut</div>                                      |
| <div>Reflection/Transmission Ratio (R/T):<br/>70/30</div>      |
| <div>Substrate: <input type="checkbox"/><br/>Float Glass</div> |
| <div>Surface Flatness (P-V):<br/>4 - 6λ</div>                  |
| <div>Surface Quality:<br/>80-50</div>                          |
| <div>Thickness (mm):<br/>1.00</div>                            |
| <div>Type:<br/>Standard Beamsplitter</div>                     |
| <div>Wavelength Range (nm):<br/>400 - 700</div>                |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |
| <div>Reach 235:<br/><a href="#">Compliant</a></div>             |