

## 20 x 28.28 x 2.5mm Elliptical Beamsplitter 50R/50T



Stock **#27-609** CLEARANCE 3-4 DAYS

- 1 + **£21.21**

ADD TO CART

|        |
|--------|
| Qty 1+ |
| £21.21 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

Clear Aperture (%):  
80.00

Coating Specification:  
Surface 1: Dielectric, ±5% R/T @ 550nm  
Surface 2: AR ¼λ MgF<sub>2</sub> @ 550nm

Dimensional Tolerance (mm):  
±0.25

Dimensions (mm):  
20.0 x 28.28

Major Axis (mm):

|                                                              |
|--------------------------------------------------------------|
| 28.28                                                        |
| Minor Axis (mm):<br>20.00                                    |
| Reflection (%):<br>50.00                                     |
| Substrate: <input type="checkbox"/><br><a href="#">N-BK7</a> |
| Thickness (mm):<br>2.50                                      |
| Thickness Tolerance (mm):<br>±0.25                           |
| Transmission (%):<br>50.00                                   |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |

---