

203 x 254mm Sandblasted Glass



Stock **#02-147** 20+ In Stock

-

1

+

£46⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£46.40 each
Qty 11+	£36.60 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Ground Glass Diffuser

Type:

Physical & Mechanical Properties

203.00 x254.00

Dimensions (mm):

1.60

Thickness (mm):

203.00	Width (mm):
254.00	Length (mm):
Optical Properties	
Float Glass	Substrate: ☐
350 - 2000	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Large Sizes Available
- 120-Grit Sandblast
- Economically Priced

Commercial Quality Sandblasted Glass is finely etched on one side to allow improved light diffusion. With a 120-grit sandblast spray, it is ideal for use in rear projection screen systems.