

203.2 x 203.2 x 3mm High Efficiency Window



Stock #21-330 3-4 DAYS

- 1 + **£51.00**

ADD TO CART

Qty 1-5
£51.00
Qty 6+
£40.80
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Bevel:

Protective as needed

Clear Aperture (%):

≥90

Clear Aperture CA (mm): 182.88 x 182.88
Dimensions (mm): 203.20 x 203.20
Thickness (mm): 3.00 ±0.25
Coating: BBAR (425-700nm)
Coating Specification: Ravg ≤0.5% @ 425 - 700nm
Edges: Seamed
Substrate: Float Glass
Surface Quality: 80-50
Transmission (%): 95.6 Average (typical)
Type: Protective Window
Wavelength Range (nm): 425 - 700
Length (mm): 203.20
Width (mm): 203.20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant